



Editorial Contact:  
Patty Hoffman  
Padilla Speer Beardsley  
Tel: 612-455-1781  
Email: [phoffman@padillaspeer.com](mailto:phoffman@padillaspeer.com)

For a high resolution image, visit:  
[www.colder.com/ns212photos](http://www.colder.com/ns212photos)

## **Colder Products Company NS212 Couplings Deliver Cost-Efficient, High-Flow Fluid Transfer With Greater Chemical Resistance**

*Easy-to-Use Couplings Deliver a Small Footprint in a Wide Range of Applications*

**St. Paul, Minn. – Nov. 3, 2011** – [Colder Products Company](http://www.colder.com) has introduced the [NS212](#) quick disconnect couplings to meet the need for smaller, cost-effective non-spill fluid connectors in a wide range of applications. NS212 couplings give users increased versatility and broader chemical compatibility for printing and ink management, electronic cooling, analytical instrumentation, and other applications.

“Our customers use a wide range of chemicals in applications where even one spilled drop of fluid poses a risk to equipment or operators,” said Dennis Downs, business unit manager, industrial markets. “The NS212 couplings address these potential hazards in a compact and easy-to-use solution with a unique non-spill design that delivers cost-efficient, high-flow fluid transfer in a small footprint. It builds on our industry-leading platform of non-spill quick disconnect couplings.”

The NS212 couplings offer an easy, twist-to-connect locking mechanism and double-sided non-spill shutoff valves in a space-saving design suitable for use in a wide range of applications. The new couplings also feature very low air inclusion – air induced into the coupling upon connection – minimizing contaminants and reducing the need to purge fluid lines.

Colder NS212 Series quick disconnect couplings offer hose barb and pipe thread terminations and are available for tubing in 1/8" (3.2mm) and 1/4" (6.4mm) ID. Configurations include pipe thread, in-line and panel mount. The ferruleless compression terminations connect to 1/4" OD (6.4mm) and 0.17" ID (4.3mm) semi-rigid tubing. Pressure ranges from vacuum to 45 psi (3.1 bar), and operating temperatures range from 32° F (0° C) to 120° F (49° C).

For more information about available options and order quantities, please contact Colder Products Company Inside Sales at 651-645-0091 or 800-444-2474.

###

(more)

**About Colder Products Company**

Colder Products Company is a leading provider of quick disconnect couplings to industrial, life sciences, chemical, and packaging markets. For a free catalog CD or more information, contact: Colder Products Company, 1001 Westgate Drive, St. Paul, MN 55114. Phone: 651-645-0091. Toll-free: 800-444-2474. Fax: 651-645-5404. Web: [www.colder.com](http://www.colder.com).

*CPC, Colder Products and Colder Products Company are registered trademarks  
with the U.S. Patent & Trademark office.*